

BY*PAS VIBRA 7100-RI

NON-CAUSTIC, VIBRATORY METAL CLEANING DETERGENT w/ RUST INHIBITOR

DESCRIPTION:

Concentrated liquid detergent w/ rust inhibitor designed for use in vibratory washers safely penetrates, loosens, and emulsifies stamping and drawing fluids from all metal part surfaces leaving them clean and shiny.

CONTAINER AVAILABILITY:

30-55 Gallon Drums and 275 Gallon Totes

PHYSICAL PROPERTIES:

Physical Form	Aqueous
Color	Yellow
Odor	Detergent
Solubility in Water	Complete
Foam Profile	High
Specific Gravity	1.03-1.06
pH of concentrate	13.0

CAUTION: EYE & SKIN IRRITANT

Contains: Sodium Metasilicate, Sodium Nitrite & Surfactants: wear eye protection and gloves when handling this product and other cleaning products. Keep lids sealed when not in use and refer to the MSDS for further safety information.

ADVANTAGES:

Caustic free solution is safe on all metal surfaces!

Super concentrated detergent package and mild alkalinity removes oils, dry lubricants and other contaminants completely!

Produces rapid high flash foam with good lubricity allows parts and media to roll efficiently for the best polishing and cleaning effect! Extends media life!

Added rust inhibitor package!

VOC, phosphate and phenol FREE!

Readily Biodegradable!

APPLICATIONS:

Vibratory machines, ultra-sonic, soak tank

DILUTION RATIO'S:

Heavy Cleaning: 5-7% product in water

Medium Cleaning: 3-4% product in water

Light Cleaning: 1-2% product in water

Heat solution water to 120-160°F using softened or RO. Rinse after thoroughly!



TECHNICAL bulletin

TAKE ONE PASS WITH
BY*PAS
SUPERIOR CONCENTRATE®
1 (800) 346-1028